Metal WIRE, MOUNTED BRUSH

It solves injection residues, also it is very successful for cleaning deep burrs and EDM Erosion Traces (with 14 micron diamond paste) during polishing process. Pls. try it..!

	Conical Wire, Mounted Brush Yellow/ Brass Wire Shaft: 2.35 or 3 mm **Order : STF158**
	Conical Wire, Mounted Brush Yellow/ Brass Wire Shaft: 2.35 or 3 mm **Order : SMF158**
	Wire Disc, Mounted Brush Yellow/ Brass Wire Shaft: 2.35 or 3 mm **Order : STF222**
	Wire Disc, Mounted Brush Yellow/ Brass Wire Shaft: 2.35 or 3 mm **Order : SMF222**
	Pen, Wire Mounted Brush Inox / Metal Wire Shaft: 2.35 or 3 mm **Order : STF148**
	Pen, Wire Mounted Brush Inox / Metal Wire Shaft: 2.35 or 3 mm **Order : SMF148**



Adhesive Emery /Mounted Rubber

Angular grinder having adjustable speed makes levelling on larger surfaces and precision operations on contours thanks to flexibility of holder. **DZ**

Order	Ø Dia.	Emery	Rubber	Shaft
DZ 10	Ø 10		Ø 10	
DZ 18	Ø 18	# 080	Ø 18	
DZ 30	Ø 30	# 120	Ø 30	**3 mm**
DZ 45	Ø 45	# 220	Ø 45	
DZ 70	Ø 70	# 320	Ø 70	**6 mm**
DZ 80	Ø 80	# 400	Ø 80	
DZ 100	Ø 100		Ø 100	
DZ Set	5 + 5 Coarse / Fine Emery+ Holder			

* At order, pls. specify shaft measure and emery sand.

SPIRAL BAND Holder +Emery

SMALL SIZE SET PACKING **SHAFT 3 mm** ML

It is sold in cylindrical wound emery cloth and rubber holder package: 5 + 5 Thick / Thin Emery + Rubber Set. (10 Emery + Rubber)

SPIRAL BAND Set or As Unit

Set	Order	Rubber	Emery
5 Pieces Emery 120 Sand	**ML.04**	Ø 4	# 120
	ML.05	Ø 5	# 320
5 Pieces Emery 320 Sand	**ML.06**	Ø 6	# 400
	ML.08	Ø 8	# 600
1 Piece Rubber Holder	**ML.10**	Ø 10	# 1000

* As per request: Emery & Rubber are available as unit.

SPIRAL BAND Holder + Emery

LARGE SIZE PIECE **SHAFT 6 mm** SBL / Z

Cylindrical wound emery cloth and rubber holder, shaft 6 mm, for larger work pieces.

Order	Emery	Sand
SPZ.12	Ø 12 x 25	
SPZ.15	Ø 15 x 25	
SPZ.20	Ø 20 x 30	# 80
SPZ.25	Ø 25 x 30	# 120
SPZ.30	Ø 30 x 30	# 220
SPZ.40	Ø 40 x 30	
SPZ.50	Ø 50 x 30	
SPZ.60	Ø 60 x 35	

Order	Rubber	Shaft-Length
SPL.12	Ø 12	Ø 6 - 60
SPL.15	Ø 15	Ø 6 - 60
SPL.20	Ø 20	Ø 6 - 60
SPL.25	Ø 25	Ø 6 - 60
SPL.30	Ø 30	Ø 6 - 60
SPL.40	Ø 40	Ø 6 - 65
SPL.50	Ø 50	Ø 6 - 65
SPL.60	Ø 60	Ø 6 - 65

* As per request: Our production on emery (Fine sand) are available.

Mounted Polishing RUBBERS

Rubbered / Soft Type - Finish Polishing

Type Form RK Shaft 3 mm					
Order	**RK04**	**RK05**	**RK06**	**RK08**	**RK10**
D x L	4 x 13	5 x 15	6 x 17	8 x 20	10 x20

Type Form RB Shaft 6 mm					
Order	**RB15**	**RB20**	**RB25**	**RB30**	**RB35**
D x L	15 x25	20 x25	25 x25	30 x30	35 x35

Mounted Polishing RUBBERS

Ceramic / Hard Type - Leveling Polishing

Type Form CK Shaft 3 mm					
Order	**CK04**	**CK05**	**CK06**	**CK08**	**CK10**
D x L	4 x 13	5 x 15	6 x 17	8 x 20	10 x20

Type Form CB Shaft 6 mm					
Order	**CB15**	**CB20**	**CB25**	**CB30**	**CB35**
D x L	15 x25	20 x25	25 x25	30 x30	35 x35



Pen / Disc Polishing Rubbers

Pen Rubber	Order	Disc Rubber	Order
Red (General)	: KK06	Red (General)	: DK06
Black (Hard)	: KS06	Black (Hard)	: DS06
Threaded Drill Chuck : DM03		Screwed Drill Chuck : VM03